
# THE REAL PROPERTY.

# Series 7400 Kraftform ESD adjustable torque screwdrivers (0.1-3.0 Nm) with Rapidaptor



Application: Suitable for 1/4" DIN ISO 1173-C 6,3 and E 6,3 hexagon insert

bits and Wera Series 1 and 4

**Design:** Rapidaptor rapid-in, rapid-out, rapid-spin, chuck-all and

single-hand technology, non-magnetic

**Accuracy:** ±6 % (DIN EN ISO 6789). Numerical torque value scale, audible

excess-load signal

Handle: Kraftform with non-roll feature, multi-component

	Art.No.	∯, mm	•	<del>+++ +++ </del> Nm	Nm Nm	I, mm	] <sub>*</sub>
05 <b>074780</b> 001 1)	7430 ESD	89	1/4"	0,10-0,34	0,015	142	5 <sup>7</sup> / <sub>16</sub> "
05 <b>074782</b> 001 1)	7431 ESD	89	1/4"	0,30-1,00	0,05	142	5 <sup>7</sup> / <sub>16</sub> "
05 <b>074784</b> 001 1)	7432 ESD	89	1/4"	0,90-1,50	0,05	142	5 <sup>7</sup> / <sub>16</sub> "
05 <b>074730</b> 001	7440 ESD	105	1/4"	0,3-1,2	0,05	155	6"
05 <b>074731</b> 001	7441 ESD	105	1/4"	1,2-3,0	0,10	155	6"

<sup>1)</sup> With attachable magnifying glass, dramatically improving visibility.



# **Rapidaptor**

### Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

# Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

#### Chuck-all



The Rapidaptor quick-release chucks hold  $\frac{1}{4}$ " DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

### Single-hand function



Every function of the Rapidator quick-release chuck, such as inserting or releasing bits, can be carried out with one hand. This is faster, more economical and more ergonomic. There are no unnecessary manoeuvres.

## Attachable magnifying glass



Articles 7430, 7431, 7432, 7430 ESD, 7431 ESD, 7432 ESD, 7435 ESD, 7436 ESD, 1430 ESD and 1431 ESD all come with a magnifying glass. This can be easily attached on to the scale, dramatically improving visibility.